

Temperature calibrator TP M255S

TP Solid // Calibration bath // Room temperature...255 °C // RT...491 °F



TP M255S

TP M255S - Highlights

- Very easy operation with 4-button control and integrated reference temperature sensor
- PC interface with connection cable to USB for use with SIKA calibration software
- Low weight and stable handle for easy transport
- Optional accessory: Transport case with or without trolley
- Qualified for SIKA Gold Service
- Especially suitable for calibration of devices under test with special sensor geometry. DUTs are simply immersed in the calibration liquid, no calibration insert with specific bore hole pattern is required.

TP Solid

With the temperature calibrators of the TP Solid series, the main focus is on **flexibility**: In addition to **dry block calibrators**, they also include **calibration baths**, with which almost any temperature sensor can be calibrated irrespective of its shape. Both can be operated **easily and intuitively**. When being used as fluid bath calibrator, the temperature sensors are directly immersed into the calibration liquid. This creates a direct temperature link

between the calibrator and the devices under test without insulating air gap. All TP Solid temperature calibrators are additionally equipped with a **serial interface for computer-assisted monitoring** of the calibration process. This flexibility in combination with the easy operation make the TP Solid series ideal for **use in machinery and plant engineering**.

SIKA temperature calibrators

Temperature calibrators are used for the verification of the functionality and calibration of temperature measuring devices and temperature sensors. As the sole German manufacturer of these devices, we develop and produce our "Made in Germany" temperature calibrators with a special focus on **long-term reliability** and **utmost accuracy** in combination with **easy operation**. We can rely on more than 40 years of experience in doing this: SIKA's **first dry block temperature calibrator** was launched all the way back in 1980.

Every SIKA temperature calibrator is meticulously tested for **accuracy** and **stability**. This is attested by our standard calibration certificate, which we issue with every temperature calibrator, or by means of an optional DAkkS calibration certificate [German accreditation body]. This is to guarantee that you receive a **perfect product** which can be traced back to national and international temperature measurement standards.

Features

Easy operation

- The TP M255S can be operated with only four buttons: Two arrow buttons for setting the target temperature, one button for confirmation and one return button
- Thus, temperatures can be set as easily as, for example, in the air conditioning system in your car
- Any operational errors can be nearly excluded. You do not need any specifically trained staff or time-consuming briefings



TT-Scan multi-channel measuring instrument

- To calibrate devices under test that do not have their own temperature display, you need to connect them to a measuring instrument
- This is done by our TT-Scan multi-channel measuring instrument: With this instrument, you can calibrate up to eight DUTs without a display unit of their own
- The TT-Scan and the temperature calibrator are connected to a PC or laptop on which the temperatures of the DUTs are output via our PC software and evaluated.
- Compatible with DUTs with all common signals: Resistance thermometer, thermocouple and current signals
- The simultaneous calibration of several DUTs enables great time savings

SIKA Gold Service

SIKA Gold Service provides a comprehensive service package for the regular recalibration of your temperature calibrator. You will benefit from exclusive savings and discounts as well as special promotions reserved to SIKA Gold Service members.

- You will save 33% in the recalibration of your temperature calibrator
- You will receive a 10% discount on any repairs that may become necessary
- You will receive preferential invitations to product presentations, symposia, practice days and exclusive training offers

Register now and benefit from the SIKA Gold Service: gold-service.sika.net



Technical data

TP M255S		
Temperature range	Room temperature...255 °C	Room temperature...491 °F
Calibration volume	Ø 60 x 170 mm	
Calibration bath		
Display accuracy	±0.2 °C	±0.36 °F
Temperature stability	±0.05 °C	±0.09 °F
Resolution of the temperature display	0.01 °C in the range -9.99...99.99 °C, else 0.1 °C	0.01 °F in the range -9.99...99.99 °F, else 0.1 °F
Reference temperature sensor	internal, fixed installation	
PC interface	RS485 (calibrator) to USB (PC)	
Dimensions		
→ Width	150 mm	
→ Height	330 + 70 mm	
→ Depth	270 mm	
Weight	Approx. 7.5 kg	
Power supply		
→ Standard	230...240 VAC, 50 / 60 Hz	
→ Optional	100...230 VAC, 50 / 60 Hz	
Power consumption	Approx. 1000 W	
Display		
Display	2-line, 4-digit digital display, red / green, unit °C / °F	

Article numbers

To order a complete calibrator, you need two order numbers:

1. Calibrator
2. Linearisation

In addition, depending on your individual calibration requirements, you can order additional calibration inserts, necessary certificates and other accessories.

1. Calibrator					
Temperature range		Function	Calibration insert [mm]	Power supply	Article number
Room temperature...255 °C	RT...491 °F	Calibration bath	Ø 60 x 170	230 V	EPMB250S601500
Room temperature...255 °C	RT...491 °F	Calibration bath	Ø 60 x 170	100...230 V	EPMB250S601503

Notice: Every "linearisation" article number with 13 digits starts with "EK1", while the following letters ("short designation") indicate the selected calibration function. You may also select several functions of one category. Please indicate the calibration functions in alphabetical order and fill in any possibly remaining positions with "0".

2. Linearisation											
Calibration function			Calibration insert / calibration medium				Reference temperature sensor			Short designation	
Calibration bath (Direct filling)			20 cSt	7...220 °C	44.6...428 °F		internal			R	
			50 cSt	50...270 °C	122...518 °F		internal			T	
Example article number linearisation											
Function:		1	2	3	4	5	6	7	8	9	10
Article number:	EK1	T	0	0	0	0	0	0	0	0	0

3. Calibration certificate - Select your calibration certificates as needed	Article number
Each calibrator is already delivered with a standard calibration certificate (3 test points).	
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 1st calibrator function	EKTPWP1FKT
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 2nd calibrator function	EKTPWP2FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 1st calibrator function	EKTPDAKKS1FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 2nd calibrator function	EKTPDAKKS2FKT
Each additional test point DAkKS calibration certificate	EKTPDAKKSZUSP
SIKA Gold Service works calibration certificate	EKTPGOLDWP
SIKA Gold Service DAkKS	EKTPGOLDDAKKS

4. Accessories	Article number
Transport case without trolley	EZTPKOFFER020
Transport case with trolley	EZTPKOFFER020TG
Tripod (holder for devices under test)	EZTPMSG00000000
Calibration liquid (silicone oil), 50cSt	EZSÖ0500000000
PC software (without TT-Scan)	EZ999999999971
PC software (with TT-Scan)	EZ380000000001
PC connection cable: temperature calibrator (RS485) to USB	EZ170000000002

Overview of SIKA temperature calibrators

Temperature range (RT=Room temperature)	Function	Accuracy		Features	Block dimensions [Ø mm x depth mm]	Type
-55 °C ... 200 °C -67 °F ... 392 °F	Dry block	±0.4 °C	±0.72 °F		28 x 150	TP 17200
	Dry block	±0.2 °C	±0.36 °F	PC interface	28 x 150	TP 17200S
	Dry block	±0.2 °C	±0.36 °F	Touch screen PC interface External reference sensor Integrated measuring instrument	28 x 150	TP 37200E.2
-35 °C ... 165 °C -31 °F ... 329 °F	Dry block	±1 °C	±1.80 °F		28 x 150	TP 17165M
	Dry block	±0.4 °C	±0.72 °F		28 x 150	TP 17165
	Dry block	±0.2 °C	±0.36 °F	PC interface	28 x 150	TP 17165S
	Dry block	±0.2 °C	±0.36 °F	Touch screen PC interface External reference sensor Integrated measuring instrument	28 x 150	TP 37165E.2
	Dry block	±0.4 °C	±0.72 °F		60 x 150	TP 17166
	Dry block	±0.2 °C	±0.36 °F	PC interface	60 x 150	TP 17166S
	Calibration bath	±0.1 °C	±0.18 °F	PC interface	60 x 170	TP M165S
	Dry block Air Shield Insert Calibration bath Infrared Surface	±0.3 °C ±0.099 °C ±0.1 °C ±0.5 °C ±1 °C	±0.54 °F ±0.1782 °F ±0.18 °F ±0.9 °F ±1.88 °F	Touch screen PC interface External reference sensor Integrated measuring instrument	60 x 170	TP 3M165E.2
-10 °C ... 100 °C 14 °F ... 212 °F	Dry block	±0.05 °C	±0.09 °F	PC interface	7 x 6.5 x 150	TP 17Zero
RT ... 200 °C RT ... 392 °F	Dry block	±1 °C	±1.80 °F		18 x 150	TP 18200E
RT ... 255 °C RT ... 491 °F	Calibration bath	±0.2 °C	±0.36 °F	PC interface	60 x 170	TP M255S
	Dry block	±0.3 °C	±0.54 °F	Touch screen	60 x 170	TP 3M255E.2
	Calibration bath	±0.2 °C	±0.36 °F	PC interface		
	Infrared Surface	±0.5 °C ±1 °C	±0.9 °F ±1.8 °F	External reference sensor Integrated measuring instrument		
RT ... 450 °C RT ... 842 °F	Dry block	±0.6 °C	±1.08 °F		60 x 150	TP 17450
	Dry block	±0.3 °C	±0.54 °F	PC interface	60 x 150	TP 17450S
	Dry block	±0.3 °C	±0.54 °F	Touchscreen	60 x 150	TP 37450E.2
	Air Shield Insert	±0.2 °C	±0.36 °F	PC interface		
	Infrared Surface	±0.5 °C ±1 °C	±0.9 °F ±1.8 °F	External reference sensor Integrated measuring instrument		
RT ... 650 °C RT ... 1202 °F	Dry block	±1 °C	±1.80 °F		28 x 150	TP 17650M
	Dry block	±0.8 °C	±1.44 °F		28 x 150	TP 17650
	Dry block	±0.4 °C	±0.72 °F	PC interface	28 x 150	TP 17650S
RT ... 700 °C RT ... 1292 °F	Air Shield Insert	±0.53 °C	±0.954 °F	Touchscreen PC interface External reference sensor Integrated measuring instrument	29 x 150	TP 37700E.2
RT ... 850 °C RT ... 1562 °F	Dry block	±1 °C	±1.80 °F		18 x 100	TP 18850E
400 °C ... 1300 °C 752 °F ... 2372 °F	Dry block	±2 °C	±3.6 °F	PC interface	28 x 200	TP 281300E

Subject to technical modifications and errors

